

10x20 200 Cells 1 Inch Best Seed Plants Growing Seedling



XQA Series

-
- PS
-
- 0.4 ~ 1.5
-

XQA

32 50 72 105 128 162 200 288

XQA32



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 100cc/cell
Cell No.: 4×8	Cells/sqm: 211
Size: 540×280mm	Bottom Dia.: 7mm
Height: 60mm	Material: PS

XQA50



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 62cc/cell
Cell No.: 5×10	Cells/sqm: 330
Size: 540×280mm	Bottom Dia.: 7mm
Height: 50mm	Material: PS

XQA72



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 36cc/cell
Cell No.: 6×12	Cells/sqm: 475
Size: 540×280mm	Bottom Dia.: 7mm
Height: 45mm	Material: PS

XQA105



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 21cc/cell
Cell No.: 7×15	Cells/sqm: 693
Size: 540×280mm	Bottom Dia.: 7mm
Height: 42mm	Material: PS

XQA128



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 19cc/cell
Cell No.: 8×16	Cells/sqm: 845
Size: 540×280mm	Bottom Dia.: 7mm
Height: 45mm	Material: PS

XQA162



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 15cc/cell
Cell No.: 9×18	Cells/sqm: 1071
Size: 540×280mm	Bottom Dia.: 7mm
Height: 44mm	Material: PS

XQA200



Rooting channel & Plow groove


Item: Cell Tray	Capacity: 12cc/cell
Cell No.: 10×20	Cells/sqm: 1320
Size: 540×280mm	Bottom Dia.: 7mm
Height: 40mm	Material: PS

XQA 288



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 7cc/cell
Cell No.: 12×24	Cells/sqm: 1900
Size: 540×280mm	Bottom Dia.: 6mm
Height: 37mm	Material: PS

[illegible]

□ □ □ □ □ □ □ □ □ □ -

[illegible]



Figure 1 - Mold tray showing the location of the mold cavity.




Figure 2 - Close-up view of the mold cavity showing the location of the mold cavity.

အထက်ဖော်ပြပါအတိုင်းအကျအရ 3 နှစ်အတွင်း၊ အထက်ဖော်ပြပါအတိုင်းအကျအရ၊ အထက်ဖော်ပြပါအတိုင်းအကျအရ၊
အထက်ဖော်ပြပါအတိုင်းအကျအရ၊ အထက်ဖော်ပြပါအတိုင်းအကျအရ၊ အထက်ဖော်ပြပါအတိုင်းအကျအရ၊
အထက်ဖော်ပြပါအတိုင်းအကျအရ၊ အထက်ဖော်ပြပါအတိုင်းအကျအရ၊ အထက်ဖော်ပြပါအတိုင်းအကျအရ၊
(အထက်ဖော်ပြပါအတိုင်းအကျအရ)