

50 72 104 105 128 200 288

Seed Starter

Sprouter Growing

Seed Starter

XQA Series

- 100% 100% 100% 100% 100% 100%
- PS 100% 100% 100% 100% 100% 100%
- 100% 100% 100% 100% 100% 100%
- 0.4 ~ 1.5
- 100% 100% 100% 100% 100% 100%

Seed Starter

XQA Series

32 50 72 105 128 162 200 288 -

XQA32**Rooting channel & Plow groove**

Item: Cell Tray	Capacity: 100cc/cell
Cell No.: 4×8	Cells/sqm: 211
Size: 540×280mm	Bottom Dia.: 7mm
Height: 60mm	Material: PS

XQA50**Rooting channel & Plow groove**

Item: Cell Tray	Capacity: 62cc/cell
Cell No.: 5×10	Cells/sqm: 330
Size: 540×280mm	Bottom Dia.: 7mm
Height: 50mm	Material: PS

XQA72**Rooting channel & Plow groove**

Item: Cell Tray	Capacity: 36cc/cell
Cell No.: 6×12	Cells/sqm: 475
Size: 540×280mm	Bottom Dia.: 7mm
Height: 45mm	Material: PS

XQA105**Rooting channel & Plow groove**

Item: Cell Tray	Capacity: 21cc/cell
Cell No.: 7×15	Cells/sqm: 693
Size: 540×280mm	Bottom Dia.: 7mm
Height: 42mm	Material: PS

XQA128**Rooting channel & Plow groove**

Item: Cell Tray	Capacity: 19cc/cell
Cell No.: 8×16	Cells/sqm: 845
Size: 540×280mm	Bottom Dia.: 7mm
Height: 45mm	Material: PS

XQA162



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 15cc/cell
Cell No.: 9×18	Cells/sqm: 1071
Size: 540×280mm	Bottom Dia.: 7mm
Height: 44mm	Material: PS

XQA200



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 12cc/cell
Cell No.: 10×20	Cells/sqm: 1320
Size: 540×280mm	Bottom Dia.: 7mm
Height: 40mm	Material: PS

XQA 288



Rooting channel & Plow groove

Item: Cell Tray	Capacity: 7cc/cell
Cell No.: 12×24	Cells/sqm: 1900
Size: 540×280mm	Bottom Dia.: 6mm
Height: 37mm	Material: PS




Figure 1 - Microplate showing the location of the small hole on the rim of the well.





Figure 2 - Microplate showing the location of the small hole on the rim of the well.



蛋托 - 蛋托



蛋托 - 蛋托

蛋托

蛋托

በጥናታችን ውስጥ 3 ሰዓታት በጥናታችን ውስጥ በጥናታችን ውስጥ
በጥናታችን ውስጥ በጥናታችን ውስጥ በጥናታችን ውስጥ
በጥናታችን ውስጥ በጥናታችን ውስጥ በጥናታችን ውስጥ
(በጥናታችን ውስጥ በጥናታችን ውስጥ በጥናታችን ውስጥ)